Reeds | E11012-GLD

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

A refined play of texture and proportion, this series juxtaposes vertically fluted aluminum housings with linear reeded glass tubes. Offered in Gold or Matte Black finishes, each form integrates frosted glass diffusers that soften the powerful LED illumination within. Designed for architectural flexibility, the collection includes ADA-compliant sconces, a minimalist stem-hung GU10 pendant, adjustable GU10 spotlights, and an additional flush mount. Universal dimming and commercial-grade drivers make it ideal for elevated residential, hospitality, or decorative commercial settings.



*max overall height

MEASUREMENTS

DIMENSION	: 2.25" L x 2.25" W x 17.75" H
MAX OAH	: 62.5" OAH
CANOPY	: 4.75" W x 0.25" H x 4.75" L
HANGING WEIGHT	: 2.9 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 450 Rated (360 Del.)
BULB	: 1 x 7W LED GU10 , 7W Total
BULB INCLUDED	: (Included)
DIMMABLE	: Y
CRI	: 90 CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

Black (BK)
Gold (GLD)

MATERIAL

Steel, Aluminum

RATINGS

cETLus
Dry Location

ADDITIONAL

RATED LIFE 35000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com