






PRODUCT DESCRIPTION

A line of indirect LED lighting shines back on a rough-hewn cast aluminum plate with an erosion pattern that curves slightly at its ends. The neutral 3000K color temperature casts warm lighting that creates shadows and depth on the fixtures surface. An earthly organic composition available in Matte Black and Architectural Bronze, these sconces will elevate a space whether it be used in a wet exterior application or interior. An extension of less than 4" makes these sconces ADA compliant.



*Height from center of outlet to the top of the fixture

MEASUREMENTS

DIMENSION	: 7" W x 16" H x 4" Ext
BACK PLATE	: 4.75" W x 14" H x 8" HCO
HANGING WEIGHT	: 10.8 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 220 Rated (165 Del.)
BULB	: 1 x 22W LED AC Integrated , 22W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: Y
CRI	: 90 CRI
COLOR_TEMP	: 3000K
LIGHTING_DIRECTION	: Omni

FINISHES OPTION

Architectural Bronze (ABZ)

MATERIAL

Aluminum

RATINGS

cETLus
Wet Location
ADA

ADDITIONAL

INSTALL UP/DOWN: Up/Down
RATED LIFE 35000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com