4 In. 50W Replacement Daylight (5000K) Baffle Trim LED Recessed Downlight

Features

- Highest quality energy efficient light compliant with new California Energy Commission standards
- Easily update older recessed lighting to latest energy saving LED
- 90+ high CRI color rendering light bulbs allow colors to appear more realistic and vibrant
- **Ideal usage:** Recessed Lighting



Specifications

Item Number	Item Length (In)	Item Width (In)	Item Height (In)
LEDR4B/950CA/MP/6	5	5	2.4
Bulb Base	**Fixture Type**	**Fixture Finish**	**Fixture Lens Material**
E26	Retrofit Kit	Plastic	Plastic
Fixture Mount	**Fixture Color**	**Technology**	**Brightness (LUMENS)**
Recessed	White	LED - SMD	540
Lumen Efficiency (LPW)	**Beam Angle**	**Color Accuracy (CRI)**	**Color Temperature (CCT)**
75.0	110	90	5000
Life Hours	**Life Years**	**Voltage (V)**	**Replacement (Wattage)**
50000	45.7	120	50
Annual Energy Cost ($)	**Energy Used (Wattage)**	**Battery Operated**	**Pack Quantity**
0.87	7.2	No	6
Smart	**Portable**	**Dimmable**	**Hardwire**
No	No	Yes	No
Safety Location	**CEC Compliant**	**Warranty Years**	
Wet	Title 20	5	