



Siemens Low Voltage Molded Case Circuit Breakers Panelboard Mounting 240V Circuit Breakers - Type BL, 2-Pole, 120/240VAC are Circuit Protection Molded Case Circuit Breakers. Type: BL Application: Electrical Distribution Standard: UL 489 Voltage Rating: 120/240V Amperage Rating: 45A Trip Range: Thermal Magnetic Interrupt Rating: 10 AIC Number Of Poles: 2P

General technical data	
number of poles	2
suitability for operation	Electrical Distribution
Electricity	
continuous current rated value	45 A
Model	
product brand name	SIEMENS
type of electrical connection	BOLT-ON
Mechanical Design	
depth [in]	3 in
design of the product	BL
height [in]	2 in
width [in]	3 in
General product approval	
standard	UL 489

last modified: 1/6/2021

