


## PRODUCT DESCRIPTION

Square aluminum blocks that are not only attractive but offer robust features. As a low profile LED up and down wall sconce, they provide ample illumination that complies with ADA regulations. Fitted with a 120-277V range voltage input driver, these sconces can be used in interior and exterior spaces whether residential or commercial applications call for them. Available in a variety of sizes including smaller square forms and oversized rectangular profiles, you can also select from three color options: Natural Aged Brass, Black, and White.



### MEASUREMENTS

| | |
|---|---|
| DIMENSION | : 11.75" W x 7" H x 1.5" Ext |
| MAX OAH | : |
| HANGING WEIGHT | : 3.3 lb |

### LAMPING

| | |
|---|---|
| INPUT VOLTAGE | : 120-277V |
| LUMENS | : 1,960 Rated (1,400 Del.) |
| BULB | : 2 x 14W LED DC Integrated , 28W Total |
| BULB INCLUDED | : (Integrated) |
| DIMMABLE | : Triac or ELV at 120V |
| CRI | : 90 CRI |
| COLOR_TEMP | : 3000K |
| LIGHTING_DIRECTION | : Up&Down |

### FINISHES OPTION

Black (BK)
Natural Aged Brass (NAB)
White (WT)

### MATERIAL

Aluminum

### RATINGS

cETLus
Wet Location
ADA

### ADDITIONAL

INSTALL UP/DOWN: Down
RATED LIFE 25000 Hours
OPERATING TEMPERATURE: -20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com