



JSP® Evolution® Deluxe 6161

Full Brim Hard Hat with HDPE Shell, 6-Point Polyester Suspension and Wheel Ratchet Adjustment

- High-Density Polyethylene (HDPE) shell with a full brim providing additional protection against sun, glare, rain and falling debris
- Extended back brim helps protect neck and ears from the sun's UV rays, as well as a run-off for rain and snow...short front brim shades the face while allowing excellent visibility
- Brim includes finger grips on front and rear, as well as a textured underside to reduce reflection/glare
- 6-Point suspension system with polyester textile straps offers unrivaled comfort without compromising performance
- Unique "3D Adjustment" provides a precise fit using harness depth settings...unlike any other hard hat on the US market today
- Revolution™ Wheel Ratchet is easy to use and creates a firm comfortable fit
- **WARNING:** Reproductive Harm - www.P65Warnings.ca.gov

Applications

- Construction Applications
- Road Work
- Excavation
- Industrial Applications

Technical Data

Color	White, Yellow, Hi-Vis Yellow, Blue, Red, Black, Gray, Neon Orange, Green
Sizes Available	OS
Packaging	Bagged Each
Packed	10/Case
Case Dimensions (in)	22.05 x 12.60 x 18.90
Case Weight (lbs)	11.11
Country of Origin	United Kingdom
Shell Material	HDPE
Shell	Non-Vented
Brim Style	Full
Brim Length	Standard
Size Adjustment	Wheel Ratchet
Suspension	6 Point Polyester
Sweatband	Chamlon
Size Range	53cm-63cm
Certifications	ANSI/ISEA Z89.1, TAA Compliant

Performance Data

ANSI Type	Type I
Electrical Class	Class E

Care Instructions

The unit may be cleaned with soap and warm water and dried with a soft cloth. The helmet should not be cleaned with chemical or abrasive cleaners. The helmet should be stored out of direct sunlight, away from chemicals and not exposed to extremes of temperature.

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
280-EV6161-11	Black	OS	616314814419	10616314814416	20616314814413
280-EV6161-50	Blue	OS	5038428011013	5038428812566	5038428812566
280-EV6161-40	Gray	OS	5038428173650	5038428813594	5038428813594
280-EV6161-30	Green	OS	5038428011006	5038428812559	5038428812559
280-EV6161-LY	Hi-Vis Yellow	OS	5038428011051	5038428812603	5038428812603
280-EV6161-OR	Neon Orange	OS	5038428011044	5038428812597	5038428812597
280-EV6161-60	Red	OS	5038428011020	5038428812573	5038428812573
280-EV6161-10	White	OS	5038428010986	5038428812535	5038428812535
280-EV6161-20	Yellow	OS	5038428010993	5038428812542	5038428812542