



QRP® Qualatril®

Nitrile Latex-Free Vacuum Sealed Finger Cots
ISO 5 (Class 100)

- Packaged for ISO 5 (Class 100) applications
- Average surface resistance of 5×10^9 ohms per square unit
- For use with Class II static sensitive devices (thresholds above 1000V)
- Unique, Stand-Up pouch for easy product identification
- ESD safe compliance to ANSI/ESD S20.20-2014
- For use with Class II static sensitive devices (thresholds above 1000V)
- RoHS compliant
- P3 Polar Process



ESD

Technical Data

Color	White
Sizes Available	S-XL
Packaging	Case
Packed	14400/Case
Case Dimensions (in)	19.00 x 10.00 x 12.00
Case Weight (lbs)	19.00
Country of Origin	Viet Nam
Polymer	Nitrile
Grip	Smooth
Thickness	3.5 Mil
Powder	Powder Free
Construction	ESD Safe

Performance Data

ISO Cleanroom	ISO 5 (Class 100)
Static Control Property	Static Dissipative

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
9CS	White	S	616314279416	10616314279413	20616314279410
9CM	White	M	616314279409	10616314279406	20616314279403
9CL	White	L	616314279393	10616314279390	20616314279397
9CXL	White	XL	616314279423	10616314279420	20616314279427