



Technical Data



Color	Clear
Sizes Available	OS
Packaging	Bagged Each
Packed	144 Pair/Case
Case Dimensions (in)	23.62 x 14.76 x 16.73
Case Weight (lbs)	14.77
Country of Origin	Taiwan
Lens	Clear
Frame Style	Rimless
Lens Color	Clear
Frame Fit	Universal
Lens Coating	Anti-Scratch, Anti-Fog
Bridge	Rubber
Temple	Bayonet
Base Curve	9
Certifications	ANSI Z87.1, CSA Z94.3 Certified, TAA Compliant, EN 166, EN 170, EN 172

Bouton® Optical Recon™

Rimless Safety Glasses with Clear Temple, Clear Lens and Anti-Scratch / Anti-Fog Coating

- Lightweight, rimless design provides all day comfort
- Flexible bayonet temples contain rubber pads for a secure, non-slip fit
- Adjustable rubber nosepiece provides a comfortable fit
- Clear Lens
- 9 Base curve lens
- Meets ANSI Z87.1+
- Meets CSA Z94.3
- ⚠ **WARNING:** Cancer and Reproductive Harm - www.P65Warnings.ca.gov

Applications

- General Manufacturing
- Construction Applications
- Indoor Work

SKU Information

SKU	FRAME COLOR	LENS	LENS COLOR	LENS	UPC	UPC (INNER)	UPC (CASE)
				COATING			
250-32-0010	Clear	Clear	Clear	AS/AR	616314130298	01616314130297	02616314130296
250-32-0020	Clear	Clear	Clear	AS/AF	616314130274	01616314130273	02616314130272
250-32-0021	Black	Tinted	Gray	AS/AF	616314130281	01616314130280	02616314130289
250-32-0031	Black	Gradient	Clear	AS/AF	616314130311	01616314130310	02616314130319
250-32-0226	Brown	Indoor Outdoor Blue	Clear	AS/AF	616314130304	01616314130303	02616314130302
250-32-0520	Clear	Clear	Clear	AS/FL360	616314209529	01616314209528	02616314209527
250-32-0521	Black	Tinted	Gray	AS/FL360	616314209536	01616314209535	02616314209534
250-32-0551	Black	Tinted	Light Gray	FL360	616314249884	01616314249883	02616314249882

KEY: AF = Anti-Fog / AR = Anti-Reflective / AS = Anti-Scratch / FL360 = Fogless 3Sixty / U = Uncoated