DATA SHEET

Premium Efficiency Motor: **ODP10-36-213T,** **60 Hz**

WorldWide Electric Corporation
1 (800) 808-2131
Worldwideelectric.net

Document Generated: 31-Mar-2025
Document ID:

Customer:

MOTOR INFORMATION

HP	10
RPM	3600
Phase	3
Frequency	60
Voltage	230/460
Frame Size	213/5T
Enclosure	ODP
Degree of Protection	IP23
Service Factor	1.15
Poles	2
Full Load Speed	3494
Insulation Class	F
Temp Rise	80˚C
NEMA Code Letter	H
Duty Cycle	S1 / Continuous
Slip	2.93%
NEMA Design	B
Moment of Inertia	0.542 lb.ft.^2
Locked Rotor Time (Hot)	12 seconds
Sound Pressure Level	64 dB(A)
Number of Starts	2 Cold / 1 Hot
Max Ambient Temperature	40˚C
Max Elevation	1000 m.a.s.l (3300 f.a.s.l)
Mounting	F1
Rotation	Bi-Directional
Area of Classification	Safe Area
Inverter Rating	10:1 CT / 20:1 VT
Standard	NEMA MG 1
Approvals	UL, CE

ADDITIONAL DATA

F2 Suitable	No
Shaft Material	AISI 1045
Connection Diagram	9 Lead Wye
Approximate Weight	150.4 lbs.

EFFICIENCY/POWER FACTOR

LOAD	EFF	P. F.
100%	89.5 %	0.89
75%	90.9 %	0.88
50%	91.1 %	0.84

TORQUE

FULL LOAD	LRT	BDT
15.11 lb.ft.	360 %	312 %

AMPERAGE INFORMATION

	230V	460V
Full Load Amps	23.6A	11.8A
Locked Rotor Amps	162.88A	81.44A
No Load Current	5.1A	2.55A
Usable at 208V	5.53A	

BEARING INFORMATION


DE Bearing	6308ZZ
ODE Bearing	6306ZZ
Grease Type	NSK SN7
DE Regreasing Interval	-- Hours
ODE Regreasing Interval	-- Hours
Grease Quantity	--

This document is the property of WorldWide Electric Corporation and may not be reproduced without express authorization

MOTOR DRAWING

Premium Efficiency Motor: **ODP10-36-213T**

WorldWide Electric Corporation
1 (800) 808-2131
Worldwideelectric.net



DIMENSION - INCHES

MOUNTING					A	B	C	D	G	P	O	T	AB
E	2F1	2F2	H	BA									
4.25	5.5	7	0.43	3.5	9.69	8.19	17.8	5.25	0.16	9.4	9.8	1.5	8.16

SHAFT & KEY				
S	ES	R	N-W	U
0.31	2.41	1.201	3.38	1.375

T-BOX	GND
AA	LUG
1.38	M6*P1.0

This document is the property of WorldWide Electric Corporation and may not be reproduced without express authorization

PERFORMANCE CURVES


Premium Efficiency Motor: **ODP10-36-213T**


WorldWide Electric Corporation
1 (800) 808-2131
Worldwideelectric.net

Document Generated:	31-Mar-2025
Document ID:	

Customer:

Motor Type	ODP						
Output Rating (HP)	10		FL Speed	3494			
Full Load Torque	15.11	lb.ft	LRT (%FLT)	360	460 volt FLA	11.8	
Rotor Wk^2	0.895	lb-ft^2	BDT (%FLT)	312	230 volt FLA	23.6	





This document is the property of WorldWide Electric Corporation and may not be reproduced without express authorization.

NAMEPLATE / WIRING


Premium Efficiency Motor: **ODP10-36-213T**

WorldWide Electric Corporation
1 (800) 808-2131
Worldwideelectric.net

Document Generated:	31-Mar-2025
Document ID:	

Customer:

SAMPLE NAMEPLATE DATA



Model:	ODP10-36-213T			**Encl:**	ODP						
HP:	10	**Poles:**	2	**Frame**	213/5T	**Ins Cl:**	F	**IP**	IP23		
Hz:	60	**Code:**	H	**Hz:**	50	**Design:**	B				
Volts:	230/460	**P.F.:**	0.89	**Volts:**	190/380	**DE Brg:**	6308ZZ				
Amps:	23.6/11.8	**Eff:**	89.5%	**Amps:**	27/13.5	**ODE Brg:**	6306ZZ				
RPM:	3494	**S.F.:**	1.15	**RPM:**	2906	**WT:**	150.4 lbs.				
				S.F.:	1.0						

This document is the property of WorldWide Electric Corporation and may not be reproduced without express authorization