



USB-C to HDMI & VGA 4-in-1 Docking Converter with Power Delivery

USB 3.2 Type-C Male to HDMI (4K@30Hz), VGA (1080p@60Hz), USB-A (5 Gbps) and USB-C PD (87 W) Females, Pass-through Charging, Aluminum, Space Gray

Part No.: [130691](#)

EAN-13: 0766623130691 | UPC: 766623130691

USB-C to HDMI and VGA Adapter to connect a laptop, MacBook® or PC to a dual-display setup - including USB-A peripheral and PD charging port

The USB-C to HDMI & VGA 4-in-1 Docking Converter with Power Delivery establishes a fast, simple and convenient link between newer USB Type-C equipped media source (laptop, PC, MacBook®, Chromebook™, computer, tablet, etc.) and existing HDMI and VGA displays (monitors, TVs and projectors). You'll enjoy resolutions up to 4K@30Hz on the HDMI connection, up to 1080p@60Hz on the VGA connection, or up to 1080p@60Hz on each display of a dual-display setup. Create a mini-workstation by adding any USB 3.2 Gen 1 (formerly USB 3.0) peripheral such as a mouse, keyboard, hub, external memory device and more with the integrated USB-A port. This multiport Docking Converter is easy and quick to install. No complicated configuration or setup is required to enhance the functionality of your USB-C device. Its all-in-one design achieves a compact, integrated solution that eliminates unnecessary cables, tangles and clutter to keep installations and workspaces neat and orderly.

Up to 87 W charging power with USB-C Power Delivery (PD)

The included USB-C PD port lets you charge your notebook with power up to 87 W while simultaneously charging your other mobile devices, such as smartphones or tablets, through the USB-A port. The Power Delivery function also provides faster charging than standard chargers since it determines the power needs of compatible devices and supplies it at the quickest and safest

rate.

Take your phone to the big screen

Connect any Android 9 and later smartphone that supports video output over USB-C DP Alt Mode to enjoy your apps and media even more. Watch a video on your monitor or flip through the slides of your presentation - all from your phone.

A Multiport Adapter that's made to go where you go

The very compact aluminum housing makes this USB-C to HDMI & VGA Docking Converter the perfect travel companion. With a footprint of only 62 x 40 x 15 mm (2.44 x 1.73 x 0.59 in.), it's small enough to fit in an outer notebook bag pocket, so you can create a mini-workstation for your laptop wherever you're going.

Features:

- Creates a dual-display setup, charges your devices and connects a peripheral
- Up to 4K@30Hz UHD (3840×2160) resolution on HDMI connection
- Up to 1080p@60Hz Full HD (1920×1080) resolution on VGA connection
- Dual-video output with resolutions up to 1080p@60Hz on both displays
- Supports display modes Mirror and Extended Mirror
- One USB 3.2 Gen 1 Type-A port (formerly USB 3.0) with SuperSpeed transfer rates up to 5 Gbps and charging up to 5 W (5 V / 1 A)
- USB-A port to connect mice, keyboards or portable memory devices (and more) or to charge and sync a portable electronic device
- Supports USB Power Delivery (PD) function up to 87 W; requires an external PD charger - available from Manhattan
- Compliant with DisplayPort 1.2 Alternate Mode (DP Alt Mode)
- Compatible with all USB-C DP-Alt-Mode-supported desktops, notebooks and tablets including Apple® MacBook®, Chromebook™, Pixel™ and more
- Sturdy, sleek aluminum housing, great for both desktop and travel
- Built-in, sturdy 15 cm (6 in.) cable
- Fully HDCP 1.4 compliant, backward compatible
- Lets your smartphone work like a desktop PC while also charging it (desktop setup requires devices with Android 9 or above that offer video output over USB-C)
- Plug-and-play installation; Windows®, macOS®, Chrome OS™, iPadOS® and Android™ compatible
- Three-year warranty

Specifications:

Standards and Certifications

- DP 1.2 Alt Mode over USB-C
- USB 3.2 Gen 1
- HDMI 1.4
- HDCP 1.4
- CE
- FCC
- RoHS
- REACH
- UKCA

General

- USB-A port data transfer speed: 5 Gbps
- Bus-powered operation (except charging functions)
- USB-C PD charging: 87.0 W max. (20.0 V at 5.0 A)
- USB-A charging: 5.0 W max. (5.0 V at 1.0 A)

Connections

- One USB-C 24-pin, male
- One USB-C 24-pin, female
- One USB-A 4-pin, female
- One HDMI 19-pin, female

Physical

- Dimensions (L x W x H): 62 x 40 x 15 mm (2.44 x 1.73 x 0.59 in.)
- Net weight: 42 g (1.48 oz.)
- Gross weight: 63 g (2.22 oz.)
- Cable length: 15 cm (6 in.)
- Cable diameter: 34 AWG
- Aluminum housing

Operating Environment

- Operation temperature: 0 - 45°C (32 - 113°F)
- Storage temperature: -10 - 70°C (14 - 158°F)
- Humidity (noncondensing): 5 - 90% RH

System Requirements

- Windows 7/8.1/10/11, Chrome OS, macOS, iPadOS or Android

Package Contents

- USB-C to HDMI & VGA 4-in-1 Docking Converter with Power Delivery
- Instructions

