Modular | E30175-10BK

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

A series of shade options fit a streamlined cast aluminum disc with a slight curve. Choose from Dark Sky compliant down-lights using flat lenses or from several glass lens options including Clear prismatic patterns that create domes, spheres, or cylinders. The integrated LED lights provide ample functional lighting, while the minimal forms suit both indoor and outdoor applications.



*height from center of outlet to the top of the fixture

MEASUREMENTS

DIMENSION	: 5" W x 5" H x 6.5" Ext
BACK PLATE	: 5" W x 5" H x 2.5" HCO
HANGING WEIGHT	: 2.42 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 1,280 Rated (800 Del.)
BULB	: 2 x 8W LED PCB Integrated , 8W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: Y
CRI	: 90 CRI
COLOR_TEMP	: 3000K
LIGHTING_DIRECTION	: Up/Down

FINISHES OPTION

Black (BK)

GLASS

Clear and White 10

MATERIAL

Aluminum

RATINGS

cETLus
Wet Location
CA Title 24

ADDITIONAL

INSTALL UP/DOWN: Up/Down
RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

PHOTOMETIC: Report Found Online

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com