

SELDON

B2420-VGL

FINISHES

VINTAGE GOLD LEAF

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 19.5"

Width/Diameter: 6"

Canopy/Backplate: 4.5"

Product Weight: 2.2lb

Extension: 3.75"

Top to Center: 9.75"

Canopy/Backplate Shape: Rectangle

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: No

Shade

Shade 1: Natural Woven

Shade 1 Finish: Saguran

Shade 1 Top Width: 4.5"

Shade 1 Height: 19.5"

Shade 2: Natural Woven

Shade 2 Finish: Saguran

Shade 2 Top Length: 3"

Shade 2 Top Width: 6"

Shade 2 Height: 16"



ELECTRICAL



Bulb 1

Bulb Included: N/A

Socket: Integrated LED

Bulb Type: LED

Max Wattage: 12

Bulb Quantity: 1

Bulb Included: Yes

Wire Length: 7"

Cord Type: B & W TEFLON W/ GROUND WIRE

Dimmer Type: ELV, TRIAC

Gem Box Required (2"x3"): No

Dark Sky: No

CRI: 90

Color Temp.: 2700k

Lumens: 325

Title 24: No

Field Serviceable: No

SHIPPING

Carton 1: 24" x 10" x 8"

Carton 1 Weight: 5lb

Shipping Method: Ground

Country of Origin: PH