



TEGERA® DYNAMIC STRENGTH 7776

Learn more

Impact-reducing glove, fully lined, full grain goatskin of top quality, structured, spandex, cut resistance level D, CRF® Technology, fleece, Cat. II, knuckle protection, reinforced index finger, high visibility colour, waterproof, for allround work

CHARACTERISTICS

- High level of protection
- Flexible
- Durable
- Perfect fit

FUNCTIONS

- Impact-reducing
- High visibility colour
- Reinforced index finger
- Pre-curved fingers
- Waterproof

CRF®

3rd PROTECTION

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Prevents risk of: , Cut injuries, Abrasion injuries, Blisters, Grazes, Scratches, lacerations, Contact with dirt, Contact with moisture, Contact with damp, Contact with cold

PRIMARY ENVIRONMENTS OF USE

Cut risk environments, Dark environments, Cold environments, Wet environments, Harsh environments

PRIMARY AREAS OF USE

Machine operating, Construction

PRIMARY INDUSTRIES OF USE

Oil and gas extraction

TYPE OF WORK

Medium weight

SPECIFICATION

TYPE Cold insulation gloves, Cut resistant gloves, Impact-reducing gloves
CATEGORY Cat. II
COLLECTION Dynamic Strength
PALM MATERIAL Full grain goatskin of top quality
BACK MATERIAL Spandex
LINING Fully lined
LINING MATERIAL CRF® Technology, Fleece, HPPE
LENGTH 235-285 mm
DEXTERITY 1
GRIP DESIGN Structured
COLOUR Black
PAIRS PER: BUNDLE/CARTON 3/36
DISPLAY TYPE Thread
FASTENING Hook-and-loop
CUT RESISTANCE (EN ISO 13997) Cut resistance level D
CUT RESISTANCE (EN ISO 13997) TDM: 16.8 N
INNER MATERIAL SPECIFICATION Polyester
MIDDLE MATERIAL SPECIFICATION Thermoplastic polyurethane (TPU), HPPE (High performance polyethylene)
OUTER MATERIAL SPECIFICATION Leather, Polyester

COMPLIANCE

CE Cat. II

EAC TP TC 019:2011

EN ISO 21420:2020

EN 388:2016+A1:2018 2X43DP

EN 511:2006 121

ANSI A5 CUT

ANSI 3 ABR

FEATURES

Cut protection

Warm lining

SIZE		ARTICLE NUMBER	EAN
7	S	7776-7	7340118383569
8	M	7776-8	7340118345345
9	L	7776-9	7340118345437
10	XL	7776-10	7340118345529
11	XXL	7776-11	7340118345611
12	3XL	7776-12	7340118345703

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.