Totem | E30126-144BK

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____







PRODUCT DESCRIPTION

Zigzag towers of ribbed glass and a textured black frame. The ribbed glass texture is back lit by integrated LED strips housed within that shine bright illumination against a white reflective backdrop. With a 3" extension, these wall sconces add visual interest to your interior or exterior space, and meet ADA requirements for use down corridors and other public spaces.

MEASUREMENTS

DIMENSION	: 6" W x 24" H x 3" Ext
BACK PLATE	: 6" W x 24" H x 12" HCO
HANGING WEIGHT	: 9 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 1,920 Rated (850 Del.)
BULB	: 2 x 12W LED AC Integrated , 24W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	:
CRI	: 90 CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

Black (BK)

GLASS

Clear Ribbed 144

MATERIAL

Ribbed Glass, Aluminum

RATINGS

Wet Location
ADA

ADDITIONAL

INSTALL UP/DOWN: Down
OPERATING TEMPERATURE: -20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com