



Project / Job Name: \_\_\_\_\_

Location: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Notes: \_\_\_\_\_

**65-1172 - 240/220/180 Watt LED Linear High Bay; 3K/4K/5K CCT; IP69K; 120-347 Volt; White Finish**



**GENERAL**

Company	NUVO
EA Height	3.94
EA Width	15.55
EA Length	25.0
Bulb Included	Integrated
Dimmable Text	0-10V Dimming
Material	Aluminum
Fixture Type	Linear Hi-Bay
Status	Active
Surge Protection	Built-in surge protection - 6KV
Total Harmonic Distortion	<20%
CCT Selectable	Yes
Wattage Selectable	Yes
Finish Family	White
Additional Info	Default Wattage: 240W
Amps	2.000-0.690A/1.830-0.630A/1.500-0.520A
Integrated Features	Integrated Sensor Port
Lens Finish	Opaque
Lens Material	Polycarbonate (PC)
Lensed	Yes
Power Factor	>0.9
SDS Class	LED Fixture
Product Technology	LED
Fluor Equiv	400W-570W

**ELECTRICAL**

CCT (Kelvin Temp)	3000K/4000K/5000K
Dimmable	Yes-Dimmable
Hours Rated	50000
Beam Angle (degree)	90
Color Temp	Soft White to Natural Light
CRI	80+
Dimming Type	0-10V Dimming
Operating Frequency	50/60Hz
Operating Temp	-40C (-40F) to +55C (+131F)
HID Equivalent	450W
Lumens	37600L-28900L
Volts	120V-347V
Watts	240W/220W/180W

**PHYSICAL**

Finish	WHITE
Housing Color	White

**ADDITIONAL INFO**

Warranty	5-Years
----------	---------

**PACKAGING**

UPC	045923413278
Case Cube	0.8864
Case Height	3.94
Case Length	25.0
Case Quantity	1
Case UPC	10045923413275
Case Weight	18.5
Case Width	15.55
EA Cube	0.8864
EA Height	3.94
EA Length	25.0
EA Quantity	1
EA Weight	18.5
EA Width	15.55
Pack Type	Box
Web Height	2.44
Web Length	24.21
Web Width	14.76

**COMPLIANCE**

Bug Rating	B4-U2-G2
CA Prop 65	Lead
DLC ID	S-4RH6T8
FCC Compliant	Yes
IP Rating	IP69K
Location Rating	Wet
NSF Approved	Yes
ROHS Compliant	Yes
Safety Listing	cULus - Certified
California Ban	Lawful for sale
DLC Approved	Yes
Title 20	Exempt
T24 Compliant	No