Hoopla | E24325-BKGLD

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

Rings of various sizes finished in Black are supported from a column of soft Gold. This European classic is a soft contemporary design which works in today's home decor.



*max overall height

MEASUREMENTS

DIMENSION	: 25" L x 25" W x 63" H
MAX OAH	: 93" OAH
CANOPY	: 17" W x 1.5" H x 17" L
HANGING WEIGHT	: 10.2 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 9,000 Rated (2,500 Del.)
BULB	: 6 x 15W LED DC Integrated , 90W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: 3-in-1: Triac, ELV, or 0-10V
CRI	: 90 CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

Black / Gold (BKGLD)

White/Gold (WTGLD)

MATERIAL

Aluminum, Acrylic

RATINGS

cETLus
Dry Location

ADDITIONAL

RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com