SATCO | NUVO



Project / Job Name:

Location:

Fixture Type:

Notes:

62-928 - 42W; LED Shop Light; White Finish; 4000K

GENERAL

Company	NUVO
EA Height	4.5
EA Width	49.41
EA Length	1.81
Bulb Included	Integrated
Material	Acrylic / Plastic / Metal
Fixture Type	Shop Light
Status	Active
Style	Utility
CCT Selectable	No
Wattage Selectable	No
Finish Family	White
Additional Info	Backing is metal, ends are 5V8 plastic, optical cover is acrylic.
Amps	0.350A
Has Camera	No
Integrated Features	On/Off Pull Chain
IOT Enabled	No
Power Factor	0.99
SDS Class	LED_Fixture
Indoor Outdoor	Indoor
Product Technology	LED
Incandescent Equivalent	175W
Serviceable Battery	No
Battery Indicator	No
Digital Display	No

ELECTRICAL

CCT (Kelvin Temp)	4000K
Dimmable	Non-Dimmable
Hours Rated	50000
Beam Angle (degree)	120
Color Temp	Cool White
CRI	80+
Operating Frequency	50/60Hz
Operating Temp	-4F to +122F (-20C to +50C)
Lumens	4200L
Volts	120v
Watts	42W
Connection	Plug In

PHYSICAL

Lamp Base	Integrated
Finish	WHITE
ANSI Base	Integrated
Lamp Type	Integrated LED
Fixture Shape	Linear
Mounting Procedure	Ceiling

ADDITIONAL INFO

Warranty	5-Years

PACKAGING

UPC	045923680120
Case Cube	2.4186
Case Height	8.6
Case Length	50.1
Case Quantity	8
Case UPC	10045923680127
Case Weight	23.37
Case Width	9.7
EA Cube	0.2329
EA Height	4.5
EA Length	1.81
EA Quantity	1
EA Weight	3.75
EA Width	49.41
Pack Type	Color Box
Web Height	1.56
Web Length	49.66
Web Width	4.31

COMPLIANCE

CA Prop 65	Lead
FCC Compliant	Yes
IP Rating	IP44
Location Rating	Damp
ROHS Compliant	Yes
Safety Listing	cETLus - Listed
California Ban	Lawful for sale
UL Application	LED Shop Light
DLC Approved	No
Title 20	Exempt
T24/JA8 Compliant	No

© Satco Products, Inc.
All rights reserved 2026