

PHILIPS

Home Access

Smart deadbolt

4000 series



Smart home system integrated

Z-Wave deadbolt with touchscreen

DDL240X-15HZW

Elevate your smart home effortlessly. The Philips Z-Wave smart deadbolt can be seamlessly integrated with popular Z-Wave systems, allowing you to choose how you want to enter your home and create custom automation routines.



Satin nickel

Matte black



Z-Wave



PIN code



Key



Voice guide

Works with Z-Wave systems

Works with Z-Wave systems for deeper smart home automation



3 ways to unlock

3 ways to unlock your door with ease



SmartStart

SmartStart makes your lock easy to set up



Best-in-class S2 security

S2 security keeps your smart home network safe



Auto-lock

Auto-lock as you leave



Sleek design

Sleek design decorates your front door



Away mode

Enhances your home security when you are on a trip



Easy installation

Easy installation with just a screwdriver



Specifications

Overview		Modes		Key Features	
Material	Aluminum alloy	Operation mode	Manual mode	Safety	ANSI/BHMA Grade 2
Color	Satin nickel / Matte black		Auto mode		AES128
Bolt type	Dead bolt	Security mode	Away mode		Local storage
Keyway	SC1		Privacy mode	Alarms	Low battery alarm
Connectivity	Z-Wave 800 with long range				Wrong entry limit alarm
Unlock Methods		Power			Jam alarm
Unlocking from outside	Z-Wave system	Power supply	4 AA batteries	Remote control	Remotely unlock
	PIN code	Emergency powering	Not supported	Language	English / French / Spanish
	Key	Operating Environment		Voice navigation	Real person voice navigation
Unlocking from inside	Thumb turn	Temperature	From -35 °C to 66 °C		
	Z-Wave system	Humidity	0-95%		
Max Credentials Capacity		Installation Requirements			
Master PIN code	1	Door thickness	1-3/8 to 2 inch (35-50mm)		
User PIN code	250	Opening direction	Left inside / Left outside		
			Right inside / Right outside		
		Cross bore hole	1-1/2 or 2-1/8 inch (38/54mm)		
		Backset	2-3/8 or 2-3/4 inch (60mm/70mm)		