

HADDOCK

B4628-PBR

A modern, pared-back take on a traditional lantern, Haddock combines architectural stature with artisanal materials. A solid brass frame with a Patina Brass finish provides durable support for the curved, wavy glass panel. The hammered effect of the clear glass softens the LED illumination, eliminating glare at night. Haddock is available in three sizes to suit any outdoor area.

FINISHES

PATINA BRASS

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 28"

Width/Diameter: 10.5"

Canopy/Backplate: 6.25"

Product Weight: 19lb

Extension: 10.5"

Top to Center: 3.25"

Canopy/Backplate Shape: Rectangle

Sloped Ceiling Compatible: No

Living Finish: Yes

Uplight Only: No

Shade

Shade 1: Glass

Shade 1 Finish: Clear Optic

Shade 1 Top Width: 9.25"

Shade 1 Height: 21"

ELECTRICAL



Bulb 1

Bulb Included: N/A

Socket: Integrated LED

Max Wattage: 20

Bulb Quantity: 1

Wire Length: 7"

Cord Type: B & W TEFLON W/ GROUND WIRE

Gem Box Required (2"x3"): No

Dark Sky: No

CRI: 90

Color Temp.: 2700k

Lumens: 1025

Title 24: No

Field Serviceable: Yes



SHIPPING

Carton 1: 30" x 26" x 13"

Carton 1 Weight: 28lb

Shipping Method: Ground

Country of Origin: VN