Rhythm | E24643-144GLD

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

Ablaze with omnidirectional LED light radiating from the center of perfectly ribbed spheres, the lustrous glow within accentuates the repeating pattern on the glass' exterior. With minimal hardware visible outside the glass, select from Polished Chrome or Gold to match your interior's decor.



*max overall height

MEASUREMENTS

DIMENSION	: 11.75" L x 11.75" W x 5" H
MAX OAH	: 135" OAH
CANOPY	: 11.75" W x 1.5" H x 11.75" L
HANGING WEIGHT	: 14.68263 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 810 Rated (540 Del.)
BULB	: 3 x 6W LED DC Integrated , 18W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: 3-in-1: Triac, ELV, or 0-10V
CRI	: 90 CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

Gold (GLD)

Polished Chrome (PC)

GLASS

Clear Ribbed 144

MATERIAL

Steel, Glass

RATINGS

cETLus
Dry Location

ADDITIONAL

RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com