

Previously known as: Powerflex® 80-100



Multi Purpose



Heavy Duty

Durable multi-purpose gloves, combining mechanical performance with excellent grip

- **Strengthened grip:** ActivArm[®] 80-100 work gloves possess a crinkle finish, for excellent wet and dry grip, ensuring they are a safe, productivity-enhancing choice for construction, transport, shipping and warehousing applications
- **Improved durability:** Robustness and durability are assured by these industrial gloves' sturdy natural rubber latex coating
- **Increased comfort:** Featuring an automatic knit liner that delivers an optimally tensioned inner surface, ActivArm[®] 80-100 multi-purpose gloves ensure a comfortable fit and heightened dexterity
- **Genuine versatility:** They make good work gloves as they are designed for a wide range of handling and carrying applications



Industries

- Machinery and Equipment

Applications

- Seizing rough blocs and cylinders
- Seizing and finishing structural parts
- Loading and unloading rough parts or boxes
- Picking parts and accessories
- Final assembly
- Loading raw material
- Unloading worked parts

Previously known as: Powerflex® 80-100

Key Features

- **Crinkle finish coating:** Excellent grip gloves in both dry and wet conditions
- **Tough natural rubber latex design:** For abrasion-resistant gloves
- **Knitted liner and tensioned inner surface:** Superb fit and flexibility

Performance Standards & Regulatory Compliance

REACH Compliant



Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COLOR	PACKAGE
ActivArm® 80-100	Finishing: Palm Coated Coating Material: Natural Latex Rubber Liner Material: Cotton, Polyester Cuff Style: Knitwrist	10	6, 7, 8, 9, 10, 11	235 - 280 mm/ 9.25-11.02 inches	Blue	• 12 pairs in a bag, 12 bags in a carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
 Riverside Business Park
 Blvd International, 55
 1070 Brussels, Belgium
 T: +32 (0) 2 528 74 00
 F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
 111 Wood Avenue South,
 Suite 210
 Iselin, NJ 08830, USA
 T: +1 800 800 0444
 F: +1 800 800 0445

Australia

Ansell Limited
 Level 3, 678 Victoria Street,
 Richmond, Vic, 3121
 Australia
 T: +61 1800 337 041
 F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
 (Malaysia) Sdn Bhd
 Prima 6, Prima Avenue
 Block 3512, Jaijan Teknokrat 6
 T: +603 8310 6688
 F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
 Blvd. Bernardo Quintana No. 7001-C,
 Q7001 Torre II,
 Suites 1304, 1305 y 1306,
 Col. Centro Sur, c.p. 76079
 Queretaro, Qro. Mexico
 T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
 105 Lauder
 Cowansville, QC J2K 2K8
 Canada
 T: +1 800 363 8340
 F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2022 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.