

Project Name

Location

Prepared By



SATCO S11691

15WLED/DW/6/FS/RND/FL/DD

Notes

(www) 04-30-2023 09:43:27

General

Status	Active
Wattage	11W/15W
Voltage	120V-277V
Finish	White
CCT (Kelvin)	2700K/3000K/3500K/4000K/5000K
Color Temperature	Warm White to Natural Light
Lumen Output	1050L/1350L
Indoor or Outdoor Fixture	Indoor and Outdoor

Specifications

Technology	LED
CRI	90+
Beam Angle	108
Rated Hours	50000
Operating Temperature	-20C (-4F) to +40C (+104F)
Dimmable	Yes-Dimmable
Dimming Note	Triac at 120V / 0-10V at 120-277V
Sloped Ceiling	Yes

Dimensions

Width (in.)	6.77
Height (in.)	1.34
Weight (lb.)	1.29

Compliance

Safety Listing	cETLus - Listed
Location Rating	Wet
ENERGY STAR	Yes
ES Unique ID	ESID-3994345
Air Tight Rated	Yes
IC Rated	Yes
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
California Prop 65	Lead
NEC Compliance	Clothes Closet Certified - Reg: 410.16 (A)(3) and 410.16 (C)(5)
RoHS Compliant	Yes
FCC Compliant	Yes
Canadian Standard ICES-005	Class B
SDS Sheet	LED_Fixture

Additional Information

Specification Note	Default CCT Setting: 2700K; Default Wattage Setting: 15W
Installation Notes	Plenum Rated FT6 Cable
Warranty	5 Years