

PHILIPS

Home Access

Smart deadbolt

4000 series

Philips Built-in Wi-Fi Fingerprint Touchscreen Smart Deadbolt

DDL0M1040X-1HW

Built-in smart security with 4 ways to unlock



Specifications

Overview		One-time PIN code		Unlimited	Key Features	
Material	Aluminum alloy	Traditional key		2	Safety	Meets ANSI/BHMA standard
Color	Nickel / Matte black	Modes				AES128
Bolt type	Dead bolt	Operation mode		Auto mode		Local storage
Keyway	SC1	Security mode		Away mode	Alarm	Low battery alarm
Connectivity	Built-in Wi-Fi / Bluetooth	Power				Wrong entry limit alarm
Unlock Methods		Power supply		8 AA Batteries		Jam alarm
Unlocking from outside	Fingerprint	Emergency powering		Not supported	Remote control	App unlock
	PIN code	Operating Environment				Manage user accounts
	Home Access app	Temperature		From -35°C to 66°C		Create schedule PIN codes
Unlocking from inside	Key	Humidity		0-95%		Simple sharing
	Thumb turn	Installation Requirements			Language	English / French / Spanish
	Home Access app	Door thickness		1-3/8 to 2 inch (35-50mm)	Voice navigation	Real person voice navigation
	Voice assistant	Opening direction		Left inside / Left outside	Works with voice assistant	Amazon Alexa
Max Credentials Capacity				Right inside / Right outside		Google Assistant
Fingerprint	50	Cross bore hole		1-1/2 or 2-1/8 inch (38/54mm)		
Master PIN code	1	Backset		2-3/8 or 2-3/4 inch (60mm/70mm)		
User PIN code	100					



Built-in
Wi-Fi



Built-in
Bluetooth



Fingerprint
unlock



Control
through app



PIN code
unlock



Traditional
key