



North[®] Zone[™]

Type I, Non-Vented, Cap-Style Hard Hat with HDPE Shell, 4-Point Nylon Suspension and Pinlock Adjustment

- Sleek modern HDPE shell design
- 3-level height adjustment for greater stability, balance and retention
- Removable, replaceable rear comfort cradle for improved fit and comfort
- Moisture-wicking, breathable sweatband is easily removable, washable and replaceable
- Meets ANSI/ISEA Z89.1, Type I, Class E requirements

Technical Data

Color	Yellow, Gray, Dark Blue, Hi-Vis Orange, Orange, Green, White, Red, Hi-Vis Red, Brown, Black, Pink, Tan
Sizes Available	OS
Packaging	Bagged Each
Packed	12/Case
Case Dimensions (in)	22.38 x 22.50 x 18.50
Case Weight (lbs)	14.40
Country of Origin	Mexico
Shell Material	HDPE
Shell	Non-Vented
Brim Style	Cap Style
Brim Length	Standard
Size Adjustment	Pin-Lock
Certifications	ANSI/ISEA Z89.1, CSA Z94.1 Certified, TAA Compliant

Performance Data

ANSI Type	Type I
Electrical Class	Class E

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
N10110000	Black	OS	883940248431		00883940248448
N10120000	Brown	OS	883940248455		00883940248462
N10080000	Dark Blue	OS	883940248370		00883940248387
N10090000	Gray	OS	883940248394		00883940248400
N10040000	Green	OS	883940248318		00883940248325
N10460000	Hi-Vis Orange	OS	883940248578		00883940248585
N10050000	Hi-Vis Red	OS	883940248332		00883940248349
N10030000	Orange	OS	883940248295		00883940248301
N10200000	Pink	OS	883940248530		00883940248547
N10150000	Red	OS	883940248493		00883940248509
N10100000	Tan	OS	883940248417		00883940248424
N10010000	White	OS	883940248257		00883940248264
N10020000	Yellow	OS	883940248271		00883940248288