



North[®] Zone[™]

Type I, Full Brim Hard Hat with HDPE Shell, 4-Point Textile Suspension and Wheel Ratchet Adjustment

- Sleek modern shell design
- 3-level height adjustment for greater stability, balance and retention
- Removable, replaceable rear comfort cradle for improved fit and comfort
- Moisture-wicking, breathable sweatband is easily removable, washable and replaceable
- Meets ANSI/ISEA Z89.1, Type I, Class E requirements

Technical Data

Color	Gray, Orange, Hi-Vis Yellow, White, Tan, Red, Black, Yellow, Dark Blue, Pink, Green, Hi-Vis Orange
Sizes Available	OS
Packaging	Bagged Each
Packed	12/Case
Case Dimensions (in)	25.94 x 22.50 x 18.75
Case Weight (lbs)	14.99
Country of Origin	Mexico
Shell Material	HDPE
Shell	Non-Vented
Brim Style	Full
Brim Length	Standard
Size Adjustment	Wheel Ratchet
Certifications	ANSI/ISEA Z89.1, CSA Z94.1 Certified, TAA Compliant

Performance Data

ANSI Type	Type I
Electrical Class	Class E

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
N20R110000	Black	OS	883940279602		00883940279947
N20R080000	Dark Blue	OS	883940279572		00883940279916
N20R090000	Gray	OS	883940279589		00883940279923
N20R040000	Green	OS	883940279541		00883940279886
N20R460000	Hi-Vis Orange	OS	883940279671		00883940280011
N20R440000	Hi-Vis Yellow	OS	883940279664		00883940280004
N20R030000	Orange	OS	883940279534		00883940279879
N20R200000	Pink	OS	883940279657		00883940279992
N20R150000	Red	OS	883940279633		00883940279978
N20R100000	Tan	OS	883940279596		00883940279930
N20R010000	White	OS	883940279510		00883940279855
N20R020000	Yellow	OS	883940279527		00883940279862