



Outstanding design. Incredible value. Dynamabook Satellite Pro C50-K

This 15" laptop offers all the tools you need for a productive work or study day.

Premium design, fully-loaded features and seamless performance means the Satellite Pro C50-K makes multitasking easy. Packed with features for next-level performance including 12th Gen Intel® Core™ processor, up to 32GB of super-fast DDR4 RAM and SSD storage, the latest USB Type-C™ port which provides one-click connection to your most-used peripherals and a special anti-bacterial paint coating which inhibits the growth of microorganisms such as bacteria, this slimline, narrow-bezel laptop is ready to take on any business task you throw its way, and do so in style.

At a glance*

Slender 18.95mm frame

Up to 12th Gen Intel® Core™ Processor and Iris® Xe graphics



Starting from 1.52kg



Antibacterial paint coating in Dark Blue



15.6" non reflective FHD
180 degree opening screen

Numeric keypad

Gigabit LAN, 802.11ac Wi-Fi

USB Type-C™ port



*Dependent on configuration

Makes any environment your workspace

It may be compact, but the Dynabook Satellite Pro C50-K is fully loaded with connectivity.

Its USB Type-C™ 3.1 port supports charging, external display and data transfer, all at once via the Dynabook USB-C dock optional accessory. Meanwhile, an HDMI 1.4b port provides easy sharing on external screens, and fast and reliable Gigabit LAN and 802.11ac Wi-Fi enable effortless network access.

And if you need to quickly swap files or connect peripherals, its SD card reader, pair of USB Type-A ports and built-in Bluetooth® 5.0 have you covered.

Designed to look the part

Entry-level price, executive looks.

The sleek, dark blue Satellite Pro C50-K is just 18.95mm thin and weighs only 1.52kg. Its 15.6" non reflective FHD screen takes up more than 85% of its upper surface, affording the device a compact footprint. Yet it remains a pleasure to use at the desk or on the road thanks to its ergonomic keyboard, full numeric keypad and up to 8 hour battery life*.

It also features the largest ClickPad with integrated fingerprint reader in Dynabook's portfolio, supporting Precision Touch Pad technology for accurate control, no mouse required.

*Measured with Mobile Mark™ 2018. Mobile Mark is a trademark of Business Applications Performance Corporation

The finer details

Processor	Choice of 12th Generation Intel® Core™ Processors, i3-1215U, i5-1235U, i7-1255U, i5-1240P, i7-1260P or Intel® Celeron® 7305 processor
Operating system / Platform	Windows 10 Pro and Windows 11 Pro – Dynabook recommends Windows 11 Pro
Design colour	Dark Blue
System memory	Choice of 4GB / 8GB / 16GB modules up to a maximum of 32GB DDR4 (3,200 MHz) in two fully configurable slots
Solid state drive	Choice of 512GB/1TB NVMe™ M.2 PCIe up to Gen4 and 128GB / 256GB / 512GB NVMe™ M.2 PCIe Value
Display	39.62 cm (15.6") non reflective, option of HD 220 NIT, SHARP IGZO low power FHD IPS 300 NIT / FHD IPS 250 NIT
Graphics adapter	Up to Intel® Iris® Xe Graphics
Interfaces	1 x USB 3.2 (Gen 2, 10Gbps) Type-C port supporting data transfer, power delivery and display port, 3 x USB 3.2 (Gen 1), 1x Gigabit LAN, 1 x HDMI 1.4b, 1x external headphone (stereo)/microphone combo socket, 1x micro SD™ card slot, 1 x DC-in
Webcam / Microphone	HD webcam with shutter slider and Led indicator. Face Authentication optional. Dual Mic supports beam forming and AI powered noise reduction technology

Wireless communication	802.11ax+ac+abgn (2x2), Bluetooth® 5.2
Sound system	Stereo speakers
Keyboard	Frameless matt black title keyboard with numeric keypad, antibacterial coating, ergonomical key size and key pitch. Dedicated conference call function keys
Pointing device	ClickPad with antibacterial coating
Battery technology	3-cell battery with 45Wh or 4-cell battery with 53Wh and up to 8hrs of Battery life. Quick charge technology (30 minutes charge = 4 hours of battery)
Physical dimensions	Physical dimensions 358.9 x 230.5 x 18.95mm , weight: starting from 1.52kg
Warranty	1 year European Carry-in. Dynabook also offers a large range of services to upgrade your standard warranty, please have a look at our website emea.dynabook.com/services to find the right service for your product
Bundled hardware power	Power Adapter
Security features	fTPM 2.0, Fingerprint Reader (optional), Face Authentication (optional), Security Lock slot, Camera shutter slider
Special features	180 degree hinge, anti bacterial paint coating (chassis, keyboard and clickpad), slim bezels (85% screen to body ratio)

*Mobile Mark 2018

©2022 Dynabook Europe GmbH. Product design specifications and colours are subject to change without notice and may vary from those shown. Errors and omissions excepted.

Accessories



Dynabook USB-C™ Dock
(PA5356E-1PRP)



Dynabook Adjustable Laptop Stand
(PS0106EA1STA)



Dynabook Wired Headset
(PS0129UA1HED)