Axle | E11040-24GLD

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

Suspended by an axle of Gold pins, a Clear glass orb is illuminated with a sleek continuing line of evenly diffused LED in a white acrylic cylinder. The elongated nature of the Gold metalwork is elegantly vertical in size with a pop of playful interest and light.



MEASUREMENTS

DIMENSION	: 8" L x 8" W x 22" H
MAX OAH	: 144" OAH
CANOPY	: 4.75" W x 1.75" H x 4.75" L
HANGING WEIGHT	: 2.5 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 1,050 Rated (950 Del.)
BULB	: 1 x 11.2W LED PCB Integrated , 11W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: Triac
CRI	: 90 CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

Gold (GLD)

GLASS

Clear 24

MATERIAL

Steel + Aluminum +Glass

RATINGS

cETLus
Dry Location

ADDITIONAL

SLOPE: 30
RATED LIFE 30000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com