


## PRODUCT DESCRIPTION




**MEASUREMENTS**

| | |
|---|---|
| DIMENSION | : 18" W x 2.25" H x 4" Ext |
| MAX OAH | : 2.25" W x 2.25" H |
| HANGING WEIGHT | : 1.34 lb |

**LAMPING**

| | |
|---|---|
| INPUT VOLTAGE | : 120-277V |
| LUMENS | : 500 Rated (250 Del.) |
| BULB | : 1 x 7W LED DC Integrated , 7W Total |
| BULB INCLUDED | : (Integrated) |
| DIMMABLE | : 3-in-1: Triac, ELV, or 0-10V |
| CRI | : 90 CRI |
| COLOR_TEMP | : 3000K |
| LIGHTING_DIRECTION | : Omni |

## FINISHES OPTION

Black (BK)
Gold (GLD)
Satin Nickel (SN)

## MATERIAL

Aluminum, Acrylic

## RATINGS

cETLus
Damp Location
ADA

## ADDITIONAL

INSTALL UP/DOWN: Vertical / Hori
RATED LIFE 30000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com