Handler | E21620-NAB

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

Excellently crafted mini spotlights are ideal for highlighting spaces and providing ambient, articulating light. A knurled section of aluminum tubing meets a larger smooth surfaced aluminum housing. Recessed within this housing is a high powered, low voltage LED light source. Either wire multiple in series or individually to various accessories not provided.



MEASUREMENTS

DIMENSION	: 2" W x 5.75" H x 3.5" Ext
MAX OAH	: 2" W x 2" H
HANGING WEIGHT	: 0.75 lb

LAMPING

INPUT VOLTAGE	: 24V
LUMENS	: 300 Rated (200 Del.)
BULB	: 1 x 5W LED DC Integrated , 5W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: Triac or ELV
CRI	: 90 CRI
COLOR_TEMP	: 2700K
LIGHTING_DIRECTION	: Directional

FINISHES OPTION

- Gunmetal (GM)
- Natural Aged Brass (NAB)
- White (WT)

MATERIAL

Aluminium, PMMA

RATINGS

cETLus
Dry Location
ADA

ADDITIONAL

INSTALL UP/DOWN: Up/Down
RATED LIFE 45000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com