

# Trac 12™ | System Components


## Trac 12/25 Low Voltage Track System

### Trac 12/25 Low Voltage Track System


The Trac 12/25 system combines the 25-amp capacity of 10-gauge conductors with a miniature rigid profile that can be surface mounted or pendant suspended. The system operates using remotely located 12-volt or 24-volt transformers. A maximum of 300 watts (12 volts) or 600 watts (24 volts) can be placed per circuit of track.

### Key Features

- 10-gauge solid copper conductors with 25-amp capacity
- Rigid aluminum miniature 5/8" H x 15/16" W profile
- Accepts all standard Trac 12™ luminaires
- Can be surface or pendant mounted
- Can be cut to length by installer

















Catalog #	Finish	Description
<b>TLVR 2FT WH</b>	White	2' track (actual length 20 5/8")
<b>TLVR 2FT BL</b>	Black	
<b>TLVR 4FT WH</b>	White	4' track (actual length 44 5/8")
<b>TLVR 4FT BL</b>	Black	
<b>TLVR 6FT WH</b>	White	6' track (actual length 68 5/8")
<b>TLVR 6FT BL</b>	Black	
<b>TLVR 8FT WH</b>	White	8' track (actual length 92 5/8")
<b>TLVR 8FT BL</b>	Black	



Trac 12/25 track Sections include dead-end and mounting hardware








### Electrical Feeds and Dead End

Image	Catalog #	Finish	Description	Dimensions
 End Feed Connector and Outlet Box Cover	<b>TLR21 WH</b> <b>TLR21 BL</b>	White Black	<ul style="list-style-type: none"> <li>• Allows track to be fed via remote transformer from an outlet box</li> <li>• Includes terminal block, cover and mounting plate</li> </ul>	
 End Feed Connector	<b>TLR38 WH</b> <b>TLR38 BL</b>	White Black	<ul style="list-style-type: none"> <li>• Allows track to be fed via remote transformer from above using standard 1/2" electrical connector</li> <li>• Includes terminal block feed connector and cover</li> </ul>	
 End Feed Connector and Conduit Feed	<b>TLR34 WH</b> <b>TLR34 BL</b>	White Black	<ul style="list-style-type: none"> <li>• Allows track to be fed via remote transformer with conduit through the end or top using standard 1/2" electrical connector</li> <li>• Includes terminal block feed connector, mounting plate and cover</li> </ul>	
 Pendant End Feed Connector	<b>TLR50 WH</b> <b>TLR50 BL</b>	White Black	<ul style="list-style-type: none"> <li>• Use with TLR90, TLR91 or TLR96 to feed from end of track</li> <li>• Includes terminal block feed connector, mounting plate and cover</li> </ul>	
 Outlet Box/T-Bar Ceiling Feed Canopy	<b>TLR36 WH</b> <b>TLR36 BL</b>	White Black	<ul style="list-style-type: none"> <li>• Mounts over outlet boxes or on T-Bar ceiling to feed up to four tracks</li> <li>• Includes one terminal block connector, mounting plate and cover</li> <li>• To feed more than one track, order additional TLR36TB connectors</li> <li>• Requires T-Bar clip (TLR37) for T-bar installation</li> </ul>	
 Terminal Block Connector	<b>TLR36TB WH</b> <b>TLR36TB BL</b>	White Black	<ul style="list-style-type: none"> <li>• For use with TLR36</li> </ul>	
 Dead End	<b>TLR28 WH</b> <b>TLR28 BL</b>	White Black	<ul style="list-style-type: none"> <li>• Dead end to use on extra field-cut track sections</li> </ul>	




# Trac 12™ | System Components

## Trac 12/25 Low Voltage Track System

### Track Joiners and T-Bar Attachment Clip

 Miniature Straight Connector	<b>Catalog #</b> <b>TLR23 WH</b> <b>TLR23 BL</b>	<b>Finish</b> White Black	<b>Description</b> <ul style="list-style-type: none"> <li>Joins two track sections end-to-end</li> <li>Includes terminal block connector and cover</li> </ul>	<b>Dimensions</b> 
 Adjustable Connector	<b>Catalog #</b> <b>TLR24 WH</b> <b>TLR24 BL</b>	<b>Finish</b> White Black	<b>Description</b> <ul style="list-style-type: none"> <li>Joins two track sections to form a 90-degree corner or straight coupling</li> <li>Includes two terminal block connectors, joiner wires and both 90-degree and straight covers</li> </ul>	<b>Dimensions</b> 
 Accordion Adjustable Joiner	<b>Catalog #</b> <b>TLR20 WH</b> <b>TLR20 BL</b>	<b>Finish</b> White Black	<b>Description</b> <ul style="list-style-type: none"> <li>Joins two track sections at variable angles to left, right, up or down</li> <li>Includes two terminal block connectors, joiner wires and covers</li> </ul>	<b>Dimensions</b> 
 T-Bar Attachment Clip	<b>Catalog #</b> <b>TLR37</b> <b>TLR37916</b>		<b>Description</b> <ul style="list-style-type: none"> <li>TLR37 T-Bar Clip attaches to 15/16" inverted T-bar ceiling</li> <li>TLR37916 T-Bar Clip attaches to 9/16" inverted T-bar ceiling</li> <li>Both clips are compatible with flush tile or drop tile ceilings</li> <li>Two required for 2' or 4' sections, three required for 6' or 8' sections</li> </ul>	

### Pendant Mounting Accessories

 T-Bar Ceiling Pendant Stem Feed & Mechanical Support	<b>Catalog #</b> <b>TLR90 12IN WH</b> <b>TLR90 12IN BL</b> <b>TLR90 18IN WH</b> <b>TLR90 18IN BL</b> <b>TLR90 24IN WH</b> <b>TLR90 24IN BL</b> <b>TLR90 36IN WH</b> <b>TLR90 36IN BL</b> <b>TLR90 48IN WH</b> <b>TLR90 48IN BL</b>	<b>Finish</b> White Black White Black White Black White Black White Black	<b>Description</b> <ul style="list-style-type: none"> <li>For pendant mounting Trac 12/25 to 15/16" T-bar ceilings</li> <li>12", 18", 24", 36", 48" stem lengths</li> <li>Use two for 2', 4' or 6' of track or three for 8' of track</li> <li>For electrical feed, order TLR50 Pendant End Feed Connector</li> </ul>	<b>Dimensions</b> 
 Rigid Ceiling Pendant Stem Feed & Mechanical Support	<b>Catalog #</b> <b>TLR91 12IN WH</b> <b>TLR91 12IN BL</b> <b>TLR91 18IN WH</b> <b>TLR91 18IN BL</b> <b>TLR91 24IN WH</b> <b>TLR91 24IN BL</b> <b>TLR91 36IN WH</b> <b>TLR91 36IN BL</b> <b>TLR91 48IN WH</b> <b>TLR91 48IN BL</b>	<b>Finish</b> White Black White Black White Black White Black White Black	<b>Description</b> <ul style="list-style-type: none"> <li>For pendant mounting Trac 12/25 to rigid ceilings</li> <li>12", 18", 24", 36", 48" stem lengths</li> <li>Use two for 2', 4' or 6' of track or three for 8' of track</li> <li>For electrical feed, order TLR50 Pendant End Feed Connector</li> </ul>	<b>Dimensions</b> 