
Fractal | E41562-BK

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

Fractal brings sculptural geometry to exterior lighting with an angular, faceted cast aluminum body that feels sharp, architectural, and refined. Finished in Matte Black, the form creates dramatic shadow play by day and a controlled indirect LED glow by night. Available as a downlight, up/downlight, and coordinating 3CCT step light, the collection offers a cohesive solution for walls, pathways, entries, and outdoor transitions. Minimal in profile yet bold in character, Fractal turns functional illumination into a modern architectural accent.



MEASUREMENTS

DIMENSION	: 6.5" W x 14" H x 3.25" Ext
BACK PLATE	: 5" W x 5.5" H x 7" HCO
HANGING WEIGHT	: 2.1 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 2,000 Rated (890 Del.)
BULB	: 2 x 10W LED DC Integrated , 20W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: Triac or ELV at 120V
CRI	: 90 CRI
COLOR_TEMP	: 22-27-30-35-40K
LIGHTING_DIRECTION	: Up & Down

FINISHES OPTION

Architectural Bronze (ABZ)
Black (BK)

MATERIAL

Aluminum, Glass

RATINGS

cETLus
Wet Location
ADA

ADDITIONAL

INSTALL UP/DOWN: Up & Down
RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com