

Groove 5CCT | E52724-AL

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____



PRODUCT DESCRIPTION

Our best-selling simple LED integrated rings formed out of aluminum channel. Available in your choice of Matte Black or Brushed Gold, these modern staples of lighting design are enhanced by a recessed LED downlight that is enabled with CCT Selectable features. Select from 5 color temperature settings from warm 2700K to a bright 5000K.



*max overall height

MEASUREMENTS

DIMENSION	: 24" L x 24" W x 1.25" H
MAX OAH	: 123.5" OAH
CANOPY	: 8.25" W x 2" H x 8.25" L
HANGING WEIGHT	: 1.5 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 1,890 Rated (1,100 Del.)
BULB	: 1 x 27W LED DC Integrated , 27W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: Triac CL
CRI	: 90 CRI
COLOR_TEMP	: 27-30-35-40-50K

FINISHES OPTION

Black (BK)
Brushed Aluminum (AL)
Gold (GLD)

MATERIAL

Aluminum

RATINGS

cETLus
Dry Location

ADDITIONAL

RATED LIFE 40000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com