

CARDIFF

515-35-VGL

FINISHES

VINTAGE GOLD LEAF

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 18"

Width/Diameter: 35"

Minimum Height: 23"

Maximum Height: 65"

Canopy/Backplate: 7"

Hanging Type: 1-6" / 2-12" / 1-18" Stems

Product Weight: 55lb

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: No

Shade

Shade 1: Cast Glass

Shade 1 Finish: Piastre Dark Bronze

Shade 1 Top Length: 3.75"

Shade 1 Top Width: 10.75"

Shade 1 Height: 9.5"

Shade 2: Cast Glass

Shade 2 Finish: Piastre Dark Bronze

Shade 2 Top Length: 3.5"

Shade 2 Top Width: 12.5"

Shade 2 Height: 12.5"



ELECTRICAL



Bulb 1

Bulb Included: No

Socket: E12 Candelabra Base

Bulb Type: B11

Max Wattage: 10

Bulb Quantity: 12

Bulb Included: No

Wire Length: 144"

Cord Type: B & W TEFLON W/ GROUND WIRE

Gem Box Required (2"x3"): No

Dark Sky: No

SHIPPING

Carton 1: 36" x 25" x 34"

Carton 1 Weight: 75lb

Shipping Method: Truck Only

Country of Origin: PH