






PRODUCT DESCRIPTION

An airy configuration of Clear blown glass globe shades in various sizes suspend on thin low voltage wires. Thin tubes finished in Black or Gold descend into the center of the globes where a small G4 LED lamp provides a spark of light.



MEASUREMENTS

DIMENSION	: 7" L x 7" W x 8" H
MAX OAH	: 130" OAH
CANOPY	: 6" W x 1.5" H x 6" L
HANGING WEIGHT	: 2.2 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 180 Rated (170 Del.)
BULB	: 1 x 1.8W G4 LED , 2W Total
BULB INCLUDED	: (Included)
DIMMABLE	: 3-in-1: Triac, ELV, or 0-10V
CRI	: 90 CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

Black (BK)

Natural Aged Brass (NAB)

GLASS

Clear 18

MATERIAL

Steel, Glass

RATINGS

cETLus
Dry Location

ADDITIONAL

RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com