

<b>EAN:</b>	4013288117557	<b>Size:</b>	40x16x16 mm
<b>Part number:</b>	05104664001	<b>Weight:</b>	25 g
<b>Article number:</b>	845	<b>Country of origin:</b>	CN
		<b>Customs tariff number:</b>	82075060

- Hex shaft for very good power transfer
- Vibration-free and scratch-free operation ensured
- Best surface quality of the countersink
- Long service life
- Perfect chip removal

High quality 1-flute countersink bit by Wera. For countersinking and deburring. The hexagon shaft ensures very good power transfer, vibration-free and score-free working. Perfect chip removal and long service life. 1/4" hexagon, suitable for holders as per DIN ISO 1173-D 6.3.

**Web link**

<https://www.wera.de/en/05104664001>

Wera - 845

05104664001 - 4013288117557

Wera Werkzeuge GmbH  
Korzter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)

## 1-flute countersink bit



1-flute countersink bits, 90°

Application:  
 Deburring, chamfering and countersinking

1/4" drive suitable for holders as per DIN 3126-D 6.3 (ISO 1173)

Hexagon shaft for very high torque transfer

1 tip

Guaranteed vibration-free and scratch-free operation





Optimal countersink surface quality

Long service life

Perfect chip removal

High corrosion protection

## Further versions in this product family:

				
	mm	mm	mm	
05104660001	6.30	21.00	32.0	M 3
05104661001	8.30	21.00	32.0	M 4
05104662001	10.40	21.00	34.0	M 5
05104663001	12.40	21.00	36.0	M 6
<b>05104664001</b>	<b>16.50</b>	<b>22.00</b>	<b>40.0</b>	<b>M 8</b>
05104665001	20.50	22.00	43.0	M 10

## Web link

<https://www.wera.de/en/05104664001>

Wera - 845

05104664001 - 4013288117557

Wera Werkzeuge GmbH

Korzter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: [info@wera.de](mailto:info@wera.de)