

Item Number 6136300**Lauderdale**

33 in. 40W LED Flush with Color
Temperature Selection Matte Black Finish
Frosted Acrylic Shade

Specifications

- Height: 4.75"
- Width: 32.50"
- Depth: 18.25"
- Includes 40 Watt Integrated LED
- Hours: 50000
- Life (years)*: 45.6
- Fixture Lumens: 3500
- Equivalent Incandescent Wattage: 200W
- Color Designation: Multi: 2700, 3000, 3500, 4000, 5000



Installation

Refer to instruction manual for installation and additional warnings.
Consult a qualified electrician if unsure how to proceed.

Warranty Information - 5 Year Limited Warranty

This Westinghouse Lighting Fixture is warranted against defects in material and workmanship for a period of Five Years from purchase date.

Specifications are subject to change without notice, please visit www.westinghouselighting.com for latest information.

 and Westinghouse are trademarks of Westinghouse Electric Corporation.
Used under license by Westinghouse Lighting. All Rights Reserved.

*Based on 3hrs./day

2025

Item Number **6136300**

Compatible Dimmers

Brand	Model
Lutron	DVCL-153P, DVCL-153PR-WH, MACL-153M, PD-6WCL, MRF2-6CL, TGCL-153PH-WH-C, SCL-153P, DVCL-253P, CTCL-153PH, CTCL-153P, DVCL-253P-WH, PD-10NXD, AYCL-153P
Leviton	DSL06-1LZ, C22-6672-1LW, C26-RNL06-TW, DW6HD-1BZ, RDL06-10Z, TSL06-1LW, IPL06-10Z, 6674-10W, DDMX1-BLZ, DDL06-1LZ, DW1KD-1BZ, DL1KD-1BZ, DL6HD-1BZ, R6Z-6683-1W, RNL06-10Z, R62-6674-POW, R50-IPL06-10M
Cooper	DAL06P-C1-K, AAL06-C1-K-L, SAL06P-C1-K, DAL06P-C2
Legrand	HLV703PTC, H703PNICCV4

Specifications are subject to change without notice, please visit www.westinghouselighting.com for latest information.

® and Westinghouse are trademarks of Westinghouse Electric Corporation.
Used under license by Westinghouse Lighting. All Rights Reserved.