



Technical Data



Color	Black
Sizes Available	OS
Packaging	Bagged Each
Packed	72 Pair/Case
Case Dimensions (in)	15.98 x 14.41 x 12.52
Case Weight (lbs)	10.80
Country of Origin	Taiwan
Lens	Mirror Plus
Frame Style	Full
Lens Color	Blue
Frame Fit	Universal
Lens Coating	Anti-Scratch, Anti-Reflective
Bridge	Rubber
Temple	Bayonet, Co-Molded
Base Curve	8
Certifications	ANSI Z87.1, TAA Compliant
Product Circularity	Recycled via Terracycle

Bouton® Optical Sunburst™

Full Frame Safety Glasses with Black Frame, Blue Mirror Plus Lens and Anti-Scratch / Anti-Reflective Coating

- Lightweight, full frame design offers all day comfort
- Bayonet temples are rubber co-molded for a secure fit
- Non-slip rubber nose pads provide a comfortable fit
- 8 Base curve lens
- Meets ANSI Z87.1+
- **WARNING:** Reproductive Harm - www.P65Warnings.ca.gov

Applications

- Outdoor Work
- Drivers
- Marine
- Drilling Rig

KEY: Made from recycled or bio-based Launderable Recyclable via TerraCycle®

PIP GLOBAL SAFETY | PROTECTION EMPOWERED™

AMERICAS: +1 (800) 262-5755 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | www.pipglobalsafety.com

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED. 2026-08-08

SKU Information

SKU	FRAME COLOR	LENS	LENS COLOR	LENS	UPC	UPC (INNER)	UPC (CASE)
				COATING			
250-47-0004	Black	Mirror Plus	Red	AS/AR	616314129209	01616314129208	02616314129207
250-47-0005	Black	Mirror Plus	Silver	AS/AR	616314129216	01616314129215	02616314129214
250-47-0006	Black	Mirror Plus	Blue	AS/AR	616314129223	01616314129222	02616314129221
250-47-0007	Black	Mirror Plus	Gold	AS/AR	616314129230	01616314129239	02616314129238
250-47-0020	Black	Clear	Clear	AS/AF	616314157974	01616314157973	02616314157972
250-47-0021	Black	Tinted	Gray	AS/AF	616314157547	01616314157546	02616314157545
250-47-0041	Black	Polarized	Gray	AS/AF	616314129193	01616314129192	02616314129191
250-47-1008	Brown	Mirror Plus	Green	AS/AR	616314129247	01616314129246	02616314129245
250-47-1042	Brown	Polarized	Brown	AS/AF	616314129254	01616314129253	02616314129252

KEY: AF = Anti-Fog / AR = Anti-Reflective / AS = Anti-Scratch / FL360 = Fogless 3Sixty / U = Uncoated