Lintel | E26268-TTVBZ

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

Lintel celebrates the quiet monumentality of natural stone in a clean, architectural linear form. Two slabs of travertine extend beyond the LED housing, creating a floating beam of light defined by texture, weight, and restraint. Offered in White Travertine with Natural Aged Brass, Rosso Laterite with Gunmetal, or Titanium Travertine with Antique Bronze, each piece reveals unique color variation and organic character. Available in 48" and 60" lengths, Lintel features selectable CCT from 2700K to 5000K for tailored illumination across contemporary spaces.



MEASUREMENTS

DIMENSION	: 59" L x 2.25" W x 4" H
MAX OAH	: 48.75" OAH
CANOPY	: 6.25" W x 1.25" H x 20.75" L
HANGING WEIGHT	: 12.25 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 3,400 Rated (2,800 Del.)
BULB	: 1 x 35W LED DC Integrated , 35W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: Triac or ELV at 120V
CRI	: 90 CRI
COLOR_TEMP	: 27-30-35-40-50K

FINISHES OPTION

Rosso Laterite / Gunmetal (RLGM)

Titanium Travertine / Bronze (TTVBZ)

Travertine / Natural Aged Brass (TVNAB)

MATERIAL

Stone, Steel, Acrylic

RATINGS

cETLus
Damp Location

ADDITIONAL

RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com