



Project / Job Name:

Location:

Fixture Type:

Notes:

65-895 - 75/55/35 Watt; 3K/4K/5K CCT Small LED Post Top; Bronze; 120-347 Volt



GENERAL

Company	NUVO
EA Height	7.09
EA Width	20.28
EA Length	28.74
Bulb Included	Integrated
Diameter	17.89
Fitter	3
Material	Die-cast Aluminum
Fixture Type	Post Top
Product Notes	Default Wattage: 75W
Status	Active
Surge Protection	Built-in surge protection - 6KV
Total Harmonic Distortion	<20%
Wire Color	Black
CCT Selectable	Yes
Wattage Selectable	Yes
Finish Family	Bronze
Amps	0.630-0.220/0.460-0.410/0.290-0.100A
Integrated Features	Integrated Photocell
IOT Enabled	No
Lens Finish	Opaque
Lens Material	Polycarbonate (PC)
Lensed	Yes
Photo Cell	Yes - Bypassable
Power Factor	>0.9
SDS Class	LED Fixture
Indoor Outdoor	Outdoor
Product Technology	LED

ELECTRICAL

CCT (Kelvin Temp)	3000K/4000K/5000K
Dimmable	Yes-Dimmable
Hours Rated	50000
Beam Angle (degree)	90
Color Temp	Soft White to Natural Light
CRI	80+
Dimming Type	0-10V Dimming
Operating Frequency	50/60Hz
Operating Temp	+32F to +113F (0C to +45C)
HID Equivalent	100W-175W
Lumens	10875L-4375L
Volts	120V-347V
Watts	75W/55W/35W

PHYSICAL

Lamp Base	Integrated
Finish	BRONZE
Housing Color	Bronze
ANSI Base	Integrated
Lamp Type	Integrated LED

ADDITIONAL INFO

Warranty	5-Years
----------	---------

PACKAGING

UPC	045923652905
Case Cube	2.3914
Case Height	7.09
Case Length	28.74
Case Quantity	1
Case UPC	10045923652902
Case Weight	12.98
Case Width	20.28
EA Cube	2.3914
EA Height	7.09
EA Length	28.74
EA Quantity	1
EA Weight	12.98
EA Width	20.28
Pack Type	Box
Web Height	20.75
Web Width	17.89

COMPLIANCE

Bug Rating	B3-U3-G1
CA Prop 65	Lead
DLC ID	S-41BG1L
FCC Compliant	Yes
IP Rating	IP65
Location Rating	Wet
NSF Approved	No
ROHS Compliant	Yes
Safety Listing	cULus
California Ban	Lawful for sale
DLC Approved	Yes
Title 20	Exempt
T24/JA8 Compliant	No