Easy Drive Staples


Heavy Gauge Carbon Steel • Rust Inhibitor on All Staples • High Impact Insulated Staples









Size	Catalog No.	Qty	Case	Wt. Lbs.	Applications	
1" L x ½" W 	1100-1	100	1000	55	Romex® (NMC) 2 Conductor 14 & 12 With or Without Ground	
	1100-5	500/Bx	10,000	53		
	1100-PB5M	Bucket	5,000	26		
	1100-PB10M	Bucket	10,000	53		
1½" L x 9/16" W 	1125-1	100/Bx	10,000	68	BX or Romex®3 Conductor 14, 12, & 10 WG (A) or 2 Stacked Oval Romex 14 & 12 WG (B)	
	1125-5	500/Bx	10,000	66		
	1125-PB5M	Bucket	5,000	34		
	1125-PB8M	Bucket	8,000	53		
1" L x ½" W 	1100-IN-5	500/Bx	5,000	28	Romex® (NMC) 2 Conductor 14 & 12 With or Without Ground	
	1100-IN-PB5M	Bucket	5,000	27		
	1100-IN-PB10M	Bucket	10,000	54		
¼" L x 9/16" W 	1125-IN-5	500/Bx	5,000	34	BX or Romex® 3 Conductor 14, 12, & 10 WG or 2 Stacked Oval Romex 14 & 12 WG	
	1125-IN-PB5M	Bucket	5,000	35		

Service Entrance Staples



Size	Catalog	Qty	Case	Wt. Lbs.	Applications	Specifications
1 5/16" L x ¼" W 	1150-1	100/Bx	5,000	63	Service Entrance SEU-3/6	10 Gauge Carbon Steel Tumble Deburred and Burnished Rust Inhibitor Applied During Tumbling for 55 Gal. Drum
1 9/16" L x 1 1/16" W 	1175-1	100/Bx	2,000	27	Service Entrance SEU-2/3	11 Gauge Carbon Steel Tumble Deburred and Burnished Rust Inhibitor Applied During Tumbling for 55 Gal. Drum