



| | | | |
|------------------------|---------------|-------------------------------|--------------|
| EAN: | 4013288210517 | Size: | 130x45x21 mm |
| Part number: | 05004543001 | Weight: | 154 g |
| Article number: | 8790 HMB Deep | Country of origin: | TW |
| | | Customs tariff number: | 82042000 |

- Long sockets for low-lying screwdriving, often even with protruding threaded rods in small spaces
- Hexagonal profile enables precise bolting with high power transmission and preserves the profile
- With Take it easy tool finder: colour coding by size
- Knurling at lower end to enable easy gripping when used in manual applications
- For manual and machine operation (non-impact), ball intercept ring
- Made of matt chromed chrome-vanadium

The Wera manual and machine socket (ISO 2725 part 3) can be used in manual and machine operations. With Take it easy tool finder with colour coding by size - for quick and easy identification of the required tool. Slip-proof for easy grip even with oily hands. With ball stop groove. For external hexagon screws and bolts. Made of matte chrome-plated chrome-vanadium.

Web link
<https://www.wera.de/en/05004543001>

Wera - 8790 HMB Deep
05004543001 - 4013288210517

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Long design



Thanks to the long design of the sockets, even couplings in tight spaces can be reached. Screwdriving at protruding thread rods can also be possible.

Profile-friendly power transmission



The hexagon profile offers the transmission of high forces and loads the edges of the bolt or the screw head less than a double hexagon profile. Fine-toothed ratchets also make use of a double hexagon profile superfluous, even in confined spaces, thanks to their small return angle.

Knurling



Knurling on lower end for more grip when used manually.

Chrome vanadium steel



The insert tools are suitable for high loads thanks to their chrome-vanadium steel design.

Take it easy tool finder system



Take it easy tool finder system - with profile and size colour-coding for quick and easy tool selection. Colour-coded system for hexagon drive screws (L-Keys, Zyklus bit sockets), external hex drive screws and nuts (Joker wrenches, Zyklus sockets and Zyklus bit sockets with holding function), and TORX® drive screws (L-Keys, Zyklus bit sockets).





Web link

<https://www.wera.de/en/05004543001>

Wera - 8790 HMB Deep
05004543001 - 4013288210517

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Further versions in this product family:

| | |  |  |  |  |
|--------------------|--------------------|---|---|---|---|
| | | mm | mm | mm | mm |
| 05004530001 | leuchtpink_232C | 8.0 | 64.0 | 12.2 | 17.0 |
| 05004531001 | gruen_363C | 9.0 | 64.0 | 13.5 | 17.0 |
| 05004532001 | leuchtgelb_yellowC | 10.0 | 64.0 | 14.5 | 17.0 |
| 05004533001 | cyan_2985C | 11.0 | 64.0 | 15.7 | 17.0 |
| 05004534001 | schwarz_blackC | 12.0 | 64.0 | 16.5 | 18.0 |
| 05004535001 | tuerkis_339C | 13.0 | 64.0 | 19.0 | 17.0 |
| 05004536001 | pink_241C | 14.0 | 64.0 | 20.0 | 18.0 |
| 05004537001 | weiss | 15.0 | 64.0 | 22.0 | 20.0 |
| 05004538001 | violett_2735C | 16.0 | 64.0 | 22.0 | 20.0 |
| 05004539001 | rot_200C | 17.0 | 64.0 | 24.0 | 22.0 |
| 05004540001 | leuchtgruen_375C | 18.0 | 64.0 | 26.0 | 23.0 |
| 05004541001 | blau_307C | 19.0 | 64.0 | 26.0 | 23.0 |
| 05004542001 | leuchtpink_232C | 20.0 | 64.0 | 28.0 | 25.0 |
| 05004543001 | gruen_363C | 21.0 | 64.0 | 28.0 | 25.0 |
| 05004544001 | gelb_123C | 22.0 | 64.0 | 30.0 | 26.0 |

Web link

<https://www.wera.de/en/05004543001>

Wera - 8790 HMB Deep
05004543001 - 4013288210517

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de