



1/2" ID X 50' HOSE REEL, 3/8" NPT

STEELMAN®

REINFORCED

Contains a reinforcement layer to prevent bursting under pressure

ADJUSTABLE STOP

Adjustable hose stop allows for customization for how much hose stays out when fully retracted

TEMPERATURE RANGE

Can operate effectively in temperatures ranging from -40 to 180 degrees Fahrenheit

DURABLE MATERIALS

Made with durable reinforced rubber and NPT brass fittings

KINK RADIUS

0.27-Inch kink radius allows hose to bend without obstructing airflow

VERSATILE MOUNTING

Hose Reel can be mounted on the floor, wall, or ceiling to fit the users needs



SPECIFICATIONS

- 099198613079
- 1 Year Limited Warranty
- Comes with a 4:1 safety factor to ensure user safety during operation
- Compliant with RMA IP-2 regulations
- Max Pressure is 300 PSI
- Burst Pressure is 1200 PSI

MATERIALS

- Rubber
- Brass

PRODUCT #: 61307