



Technical Data

Color	Black
Sizes Available	7-11
Polymer	Butyl
Thickness	16 Mil
Lining	Unlined
Dip	Single
Length	11"
Cuff	Rolled
Grip	Smooth
Construction	Unsupported, Waterproof
Case Dimensions (in)	32.00 x 21.00 x 15.00
Case Weight (lbs)	60.01
Packed	288 Pair/Case
Packaging	Bulk Boxed
Certifications	TAA Compliant
Country of Origin	United States

North® Butyl™

16 Mil Butyl Rubber Glove with Rough Grip - 11"

- Exceptional resistance to a broad range of toxic chemicals: making it the only suitable for many critical applications
- Highly resistant to ketones (MEK: MIBK: acetone) and esters (tricresyl phosphate: amyl acetate: ethyl acetate)
- Solvent based: multi-dip manufacturing process provides multiple layers of polymer (like a glove within a glove) which results in a glove of superior quality
- Butyl provides the highest permeation resistance to vapors and gases
- Rough finish enhances grip on wet, oily or dry handling surfaces

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
B161R/7	Black	7	821812008219	821812008202	00821812008196
B161R/8	Black	8	821812008240	821812008233	00821812008226
B161R/9	Black	9	821812008271	821812008264	00821812008257
B161R/10	Black	10	821812008158	821812008141	00821812008134
B161R/11	Black	11	821812008189	821812008172	00821812008165