Clutch | E25135-92GLD

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

Designed to fit the essentials, this bath vanity series will always come in clutch. Dedicated LED illuminates the backside of a low-profile curved opal White glass sweeping upwards to a metal latch conveniently finished in your choice of Polished Chrome, Gold, and Matte Black. Make a statement without saying too much.



MEASUREMENTS

DIMENSION	: 30" W x 4.75" H x 3" Ext
BACK PLATE	: 30" W x 4.25" H x 2.5" HCO
HANGING WEIGHT	: 5.7 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 2,240 Rated (1,700 Del.)
BULB	: 2 x 28W LED PCB Integrated , 28W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: Y
CRI	: 90 CRI
COLOR_TEMP	: 3000K
LIGHTING_DIRECTION	: Directional

FINISHES OPTION

Black (BK)
Gold (GLD)
Polished Chrome (PC)

GLASS

Satin White 92

MATERIAL

Steel + Glass

RATINGS

cETLus
Damp Location
ADA

ADDITIONAL

INSTALL UP/DOWN: Horizontal
RATED LIFE 30000 Hours
OPERATING TEMPERATURE: -20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com