



2101XX

Technical Data

Color	Black
Sizes Available	8.5-10
Packaging	Boxed
Packed	32 Pair/Case
Case Dimensions (in)	33.50 x 25.50 x 26.50
Case Weight (lbs)	64.00
Country of Origin	United States
Polymer	Neoprene
Grip	Smooth
Cuff	Rolled
Length	32"
Powder	Powder Free
Thickness	15 Mil
Construction	Waterproof, Unsupported
Certifications	21 CFR, TAA Compliant

North®

15 Mil, 8" Port Hand Specific Neoprene Glovebox Glove - 32"

- Neoprene is a soft flexible material that provides high permeation resistance to vapors and gases while also providing resistance to a broad range of chemicals like oils, greases, fuels, and acetones
- Neoprene offers good elongation and high flexibility for free movements when working inside of the box
- Complies with USDA and FDA regulations, 21 CFR, for use in food processing
- Rolled bead cuff resists tearing, improves donning strength and maintains a secure seal on glovebox ports
- Available in sizes 8.5", 9.75" and 10.5" (palm diameter)
- Smooth finish for low friction, improved dexterity, and precise glovebox handling
- Made in the USA

Care Instructions

Three year shelf life when stored in original packaging in a cool dry place away from light. Recommended temperature range: 50F to 86F (10C to 30C).

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
8N1532/8H	Black	8.5	883940165691		00883940165455
8N1532/9Q	Black	9	883940165707		00883940165462
8N1532/10H	Black	10	883940165684		00883940165448