

Garant**Circular mill (without insert), Steel, Type: 20****Order data**

Order number	217400 20
GTIN	4045197216885
Item class	21Q

Description**Version:**

No. 217400 sizes 8 and 11 as well as No. 217405 size 11L without internal cooling.

Tool exchange: PowerCard

Through-coolant: yes

for insert type: 02

smallest hole $\varnothing D$: 17.5 mm

Internal $\varnothing d_1$: 12.2 mm

maximum cutting depth $S_{\max}$: 2.6 mm

Overhang L_1 : 28.7 mm

Overall length L_{tot} : 74.05 mm

Technical description

Overhang L_1	28.7 mm
Internal $\varnothing d_1$	12.2 mm
Shank type	Weldon
Overall length L_{tot}	74.05 mm
Shank $\varnothing D_s$ h6	12 mm
maximum cutting depth $S_{\max}$	2.6 mm
Set of insert screws	219821 (15 IP; 3.0 Nm)
smallest hole $\varnothing D$	17.5 mm
for insert type	02

Through-coolant	yes
Material of milling tool	Steel
Tool exchange	PowerCard
Type of product	Circular mills

Accessories

Set of insert screws 10-piece	219821
-------------------------------	--------