Project / Job Name:

Location:

Fixture Type:

Notes:



S30115 - LED Heavy Duty Lantern; 1000 Max Lumens; USB-C Rechargeable; 3.7 Volt; 4pc Tray Pack

GENERAL

Company	SATCO
EA Height	7.75
EA Width	4.25
EA Length	4.25
Material	ABS Plastic / Polycarbonate (PC) / Thermoplastic Rubber (TPR)
Fixture Type	Rechargeable Lantern
Includes	USB-A to USB-C Charging Cable
Product Notes	Integrated Rechargeable 4.2V Li-ion 20650 Battery; Power Bank: 2600mAh; Charge Time: 2HRS -or- 3 C Cell Alkaline
Status	Active
CCT Selectable	No
Wattage Selectable	No
Finish Family	Black
Additional Info	Ships in retail-ready display trays and packaging
Integrated Features	Power Bank; Dual Fuel; Carry Handle; Impact Absorbing Housing; Bottom Clasp Hook;
Lens Finish	Clear
Lens Material	Polycarbonate (PC)
Lensed	Yes
Portable Light Modes	High, Low, Medium, Strobe
Product Technology	LED
Serviceable Battery	Yes
Beam Distance (Ft)	72
Battery Indicator	Yes
Digital Display	No
Drop Impact Rating	3.28 Ft (1M)
Battery Operating Temp	+32F to +104F (0C to +40C)
Light Source Quantity	Single
Power Bank Storage	2600mAh

ELECTRICAL

CCT (Kelvin Temp)	6500K
Dimmable	Yes-Dimmable
Color Temp	Daylight
CRI	50+
Dimming Type	Only dimmable via setting selection, Step Dimming
Operating Temp	+32F to +104F (0C to +40C)
Lumens	1000L/650L/300L
Volts	3.7V
Max Lumens	1000L
Connection	USB-C Rechargeable
Charge Time	2hr
Battery Chemistry	Lithium-ion (Li-ion)
Replaceable Battery Type	20650
USB Type In	1 USB-C
USB Output Charging Power	(1) 2A 5V
USB Type Out	1 USB-A 2A
Dual Fuel	3 C-Cells Alkaline Batteries

PHYSICAL

Finish	Black / Gray / Red
Housing Color	BlackGrayRed
Mounting Procedure	Hang Hook

ADDITIONAL INFO

Warranty	1-Year
Installation Notes	Do Not Charge The Product Below 40F Or above 104F; Do Not Exceed 5V DC, 1A Charging
Portable Light Functions	Red Light Function, White Light Function

PACKAGING

UPC	045923300165
Case Cube	1.2358
Case Height	10.43
Case Length	10.5
Case Quantity	8
Case UPC	10045923300162
Case Weight	13.2
Case Width	19.5
EA Cube	0.081
EA Height	7.75
EA Length	4.25
EA Quantity	1
EA Weight	1.37
EA Width	4.25
Inner Cube	0.4294
Inner Height	9.13
Inner Length	9.09
Inner Quantity	4
Inner UPC	20045923300169
Inner Weight	6.17
Inner Width	8.94
Pack Type	Color Box
Web Height	7.44
Web Length	4.17
Web Width	4.17

COMPLIANCE

CA Prop 65	Lead
FCC Compliant	Yes
IP Rating	IPX4
ROHS Compliant	Yes
Energy Star Certified	No
T24/JA8 Compliant	No
Performance Standards	ANSI PLATO FL1

© Satco Products, Inc.
All rights reserved 2026