

ALL-IN-ONE COMBO L-BAR SEALER

MODELS SS-48ST, SS-76ST, SS-77ST

sealersales



Plug and Go: Seal and Shrink in One Step

- Compact size for small workspaces
- Micro Knife technology to seal PVC or POF
- Dual magnetic hold down
- Dual mode switch for seal only or shrink/seal
- Heavy duty plexiglass hood
- Adjustable table lowers 2" for higher products

This unique **All-In-One L-Bar Sealer and Shrink Chamber** features a Micro Knife technology to seal both PVC and POF films. With the dual magnetic hold down, the operator simply lowers the hooded chamber and the magnets apply the seal pressure to produce great seals and eliminate operator fatigue. The magnets hold the chamber closed during the shrink cycle and releases when the shrink cycle is complete. Adjustable grate lowers 3.5" to accept taller products. Complete cycle time is approximately 5-10 seconds. This unit is ideal for small workspaces without compromising performance.

SPECIFICATIONS	SS-48ST-110V	SS-76ST	SS-77ST
POWER SUPPLY	110V / 1 PH / 20 AMPS	220V / 1 PH / 25 AMPS	220V / 1 PH / 30 AMPS
WATTS	1650W	3000W	3000W
SEAL DIMENSIONS	12"W X 18.5"L	16"W X 22"L	20"W X 30"L
MACHINE DIMENSIONS	50"L X 26"W X 45"H	56"L X 30"W X 45"H	72"L X 35"W X 50"H
MAX. FILM WIDTH	20"	24"	28"
MAX. PACKAGE HEIGHT	6"	8"	10"
PRODUCTION RATE	3-5 PPM	3-5 PPM	3-5 PPM
WEIGHT	270-LBS	350-LBS	400-LBS