



Technical Data

Color	Black
Sizes Available	OS
Packaging	Bagged Each
Packed	72 Pair/Case
Case Dimensions (in)	18.90 x 8.66 x 14.96
Case Weight (lbs)	0.00
Country of Origin	Taiwan
Lens	Clear
Frame Style	Semi-Rimless
Lens Color	Clear
Frame Fit	Universal
Lens Coating	Anti-Scratch, FogLess 3Sixty
Bridge	Rubber
Temple	Bayonet, Rubber Tips
Diopter	2.00
Base Curve	8.5
Certifications	ANSI Z87.1, TAA Compliant
Product Circularity	Recycled via Terracycle

Bouton® Optical Anser™

Semi-Rimless Safety Readers with Black Frame, Clear Lens and Anti-Scratch / Fogless® 3Sixty™ Coating - +2.00 Diopter

- FogLess® 3Sixty™ enhanced hydrophobic action resists lens fogging and provides clear vision in extreme working conditions
- Magnification reader glasses are for the worker who needs to see up close
- Lightweight, semi-rimless design provides all day user comfort
- Sleek, sporty style with wraparound lens protection
- Bayonet temples with flexible rubber tips offer a comfortable, secure fit
- Soft rubber nose pads help keep the glasses in place
- Supplied with an adjustable neck cord
- 8.5 Base curve lens
- Meets ANSI Z87.1-2015 standards

Applications

- General Manufacturing
- Construction Applications
- Indoor Work

KEY: Made from recycled or bio-based Launderable Recyclable via TerraCycle®

PIP GLOBAL SAFETY | PROTECTION EMPOWERED™

AMERICAS: +1 (800) 262-5755 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | www.pipglobalsafety.com

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED. 2026-07-18

SKU Information

SKU	FRAME COLOR	LENS	LENS		UPC	UPC (INNER)	UPC (CASE)
			LENS COLOR	COATING			
250-AN-10110	Black	Clear	Clear	AS	899558001412	01616314123299	02616314123298
250-AN-10111	Black	Clear	Clear	AS/AF	899558001429	01616314123305	02616314123304
250-AN-10112	Black	Tinted	Gray	AS	899558001436	01616314123312	02616314123311
250-AN-10113	Black	Tinted	Light Blue	AS	899558001443	01616314122223	02616314122222
250-AN-10114	Black	I/O	Clear	AS	899558001450	01616314123329	02616314123328
250-AN-10115	Black	Mirror	Blue	AS	899558001467	01616314123336	02616314123335
250-AN-10116	Black	Mirror	Red	AS	899558001474	01616314123343	02616314123342
250-AN-10117	Red	Tinted	Gray	AS	899558002105	01616314123350	02616314123359
250-AN-10118	Black	IR Filter	Green	AS	899558002112	01616314123367	02616314123366
250-AN-10119	Black	IR Filter	Green	AS	899558002129	01616314123374	02616314123373
250-AN-10120	Black	Tinted	Amber	AS	899558002136	01616314123381	02616314123380
250-AN-10121	Camouflage	Tinted	Brown	AS	899558002143	01616314122230	02616314122239
250-AN-10122	Camouflage	Tinted	Amber	AS	899558002150	01616314123398	02616314123397
250-AN-10123	Camouflage	Tinted	Gray	AS	616314122255	01616314122254	02616314122253
250-AN-10124	Camouflage	Tinted	Brown	AS/AF	616314161902	01616314161901	02616314161900
250-AN-10125	Black	Mirror	Silver	AS	616314124433	01616314124432	02616314124431
250-AN-10126	Black	Tinted	Gray	AS/AF	616314146633	01616314146632	02616314146631
250-AN-10127	Camouflage	Tinted	Amber	AS/AF	616314161919	01616314161918	02616314161917
250-AN-10128	Camouflage	Mirror	Silver	AS	616314161926	01616314161925	02616314161924
250-AN-10130	Camouflage	Clear	Clear	AS	616314186219	01616314186218	02616314186217
250-AN-10131	Camouflage	Clear	Clear	AS/AF	616314186226	01616314186225	02616314186224
250-AN-10132	Black	Mirror	Smoke	AS	616314429484	10616314429481	20616314429488
250-AN-10520	Black	Clear	Clear	FL360/AS	616314232558	01616314232557	02616314232556
250-AN-10521	Black	Tinted	Gray	FL360/AS	616314232565	01616314232564	02616314232563
250-AN-10551	Black	Tinted	Light Gray	FL360/AS	616314250231	01616314250230	02616314250239
250-AN-11115	Black	Clear	Clear	AS/AF	616314267352	01616314267351	02616314267350
250-AN-11120	Black	Clear	Clear	AS/AF	616314267369	01616314267368	02616314267367
250-AN-11125	Black	Clear	Clear	AS/AF	616314267376	01616314267375	02616314267374
250-AN-52015	Black	Clear	Clear	FL360/AS	616314395017	10616314395014	20616314395011
250-AN-52020	Black	Clear	Clear	AS/FL360	616314395055	10616314395052	20616314395059
250-AN-52025	Black	Clear	Clear	FL360/AS	616314395093	10616314395090	20616314395097

KEY: AF = Anti-Fog / AR = Anti-Reflective / AS = Anti-Scratch / FL360 = Fogless 3Sixty / U = Uncoated