
Project / Job Name:

Location:

Fixture Type:

Notes:



60-8745 - Cassian; 2 Light Wall Sconce; Polished Nickel Finish; Opal Glass

DAMP LOCATION | ETL | FC | RoHS | 30,000 HOURS | 1 YEAR WARRANTY | 120 VOLT | IP 20

GENERAL

Company	NUVO
EA Height	7.0
EA Width	10.75
EA Length	13.5
Mounting Height	4.75
Mounting Length	16.13
Mounting Width	6.13
Glass Finish	Opal
Extends (in)	6.13
Material	Steel / Glass
Includes	Mounting Strap and Screws
Status	Active
Style	Modern and Contemporary
Top To Outlet	8.0
Up Down Installation	Universal
CCT Selectable	No
Wattage Selectable	No
Collection	Cassian
Finish Family	Nickel
Indoor Outdoor	Indoor
Product Technology	Lamp Dependent
Fixture Lamp Count	2
Fluor Equiv	15W
Incandescent Equivalent	90W
Serviceable Battery	No
Battery Indicator	No
Digital Display	No

ELECTRICAL

CCT (Kelvin Temp)	Lamp Dependent
Dimmable	Lamp Dependent
Hours Rated	30000
Operating Temp	-40F to +194F (-40C to +90C)
Volts	120v
Watts	13W
Connection	Hardwire

PHYSICAL

Lamp Base	G9 Double Loop
Finish	Polished Nickel
Housing Color	Polished Nickel
ANSI Base	G9
Lamp Type	T6
Fixture Shape	Round

ADDITIONAL INFO

Warranty	1-Year
Rated For Enclosed Fixture	No

PACKAGING

UPC	045923416712
Case Cube	0.5879
Case Height	7.0
Case Length	13.5
Case Quantity	1
Case UPC	10045923416719
Case Weight	3.52
Case Width	10.75
EA Cube	0.5879
EA Height	7.0
EA Length	13.5
EA Quantity	1
EA Weight	3.52
EA Width	10.75
Pack Type	Kraft Box
Web Height	4.75
Web Width	16.13

COMPLIANCE

CA Prop 65	Lead
FCC Compliant	Yes
IP Rating	IP20
Location Rating	Damp
NSF Approved	No
ROHS Compliant	Yes
Safety Listing	cETLus
California Ban	Lawful for sale
Energy Star Certified	No
Title 20	Exempt
T24/JA8 Compliant	No

© Satco Products, Inc.
All rights reserved 2026